

Peak Performance and Durability

What is the ETL Performance test?

- Hot Water Immersion
- Water Resistance
- Heat & Humidity
- Controlled Condensation
- Effects on Adhesive Bonds



Lasts a minimum of 10x longer than non ETL verified PVC Coated Conduit

- ✓ Rigid Conduit - Made in USA 
- ✓ Unsurpassed Corrosion Resistance
- ✓ Durability
- ✓ Peak Performance
- ✓ Reduced Downtime
- ✓ Increased Safety
- ✓ Industry Leading Value
- ✓ Unmatched Service

More Safety and Less Downtime

What are UL 6 Safety Standards

Calbond's protective coating of zinc be evenly applied to the exterior surface of the GRC conduit, adhering firmly without blistering or defects.

- Rigid Metal Conduit Safety
- Protective Zinc Coating
- Calbond Special Bonding Agent



Full Line PVC Coated Conduit, Fittings and Accessories

Affordable protection for Electrical Raceway Systems in Harsh Environments

Rigid Conduit

- 12 Trade Sizes From 1/2" - 6"
- Exterior PVC Coating Thickness min. 0.040"
- Interior Urethane Coating Thickness min. 0.002"
- Both Zinc and PVC Coatings are UL Listed as Primary Coatings
- Fully Undisturbed Zinc Coating Under Its PVC Coating
- Fulfills The Requirement Of NEMA RN-1



Elbows, Nipples, Couplings

- 12 Trade sizes from 1/2" - 6"
- Exterior PVC coating thickness min. 0.040"
- Interior urethane coating thickness min. 0.002"
- All diameters and radius available



Conduit Fittings

- 10 Trade sizes from 1/2" - 4"
- Exterior PVC coating thickness min. 0.040" Form 7 & 8 in all config.
- Encapsulated stainless steel screws
- Added protection with urethane interior coating
- Flexible overlapping sleeves ensure a tight seal at every connection
- Conduit Bodies
- Hubs
- Liquidtight Connectors
- Malleable Fittings



Device Boxes and Covers

- 3 Trade sizes from 1/2" - 1"
- FD, FDC, FDCT, FS, FSC, FSCA
- Added protection with urethane interior coating
- Flexible overlapping sleeves



Hazardous Location Fittings

- 10 Trade sizes from 1/2" - 4"
- Exterior PVC coating thickness is a min. 0.040"
- GUAC, GUAT, GUAX, GUAB, GUAL, GUAD
- GUAN, GUAW, EYS, EYD, UNF, UNY
- Added protection with urethane interior coating
- GUA Junction Boxes
- Seal Offs
- Unions



Strut and Strut Accessories

- Strut: Standard, Punched, Slotted, Back to Back & Half Size
- Straps are sized to fit Calbond Conduit
- Clamps, Right Angle, Edge and Parallel
- U Bolts
- Conduit Hangers

